



# LATEX STRONG 44-161





## **CHARACTERISTICS**

- · Powdered latex glove
- · Smooth inside
- · Supple and pleasant to wear
- · Very easy to put on thanks to rolled edge
- · Suitable for the right and left hand (ambidextrous)
- · Suitable for contact with many foods
- · Meets the EN 455 requirement for medical examination gloves
- · Length: 240 mm and thickness: 0.10 mm
- $\cdot$  Weight: 6.5 grams (+/- 0.3 grams)
- AQL 1.5 (EN 374)
- · Gloves are for single use only
- · Packed per 100 pieces in a dispenser

Article number: 1.44.161.00

# SUITABLE FOR ACTIVITIES IN E.G.

- · Food industry
- Agri
- Hospitality
- $\cdot$  Maintenance
- · Cleaning
- Automotive

# COLOUR

Blue

### **OTHER AVAILABLE COLOURS**

Natural (art.no. 1.44.160.00)

## SIZES

7/S to 10/XL incl.

# **PACKAGING**

- · 100 pieces per dispenser
- · 10 dispensers in a case

EN ISO 374-1:2016 +A1:2018/Type C





EN ISO 374-5:




EN 455

**C € 1639** EN 420:2003+A1:2009



#### **PRODUCT INFORMATION**

SIZE	ARTICLE NO.	EAN CODE 100 PIECES (DISPENSER)	EAN CODE 10 DISPENSERS (CASE)		
7/S	1.44.161.07	8718249008344	8718249008351		
8/M	1.44.161.08	8718249008368	8718249008375		
9/L	1.44.161.09	8718249008382	8718249008399		
10/XL	1.44.161.10	8718249008405	8718249008412		



#### **CLARIFICATION OF PICTOGRAMS**

Protection against chemicals and micro-organisms

EN ISO 374-1:2016/Type B					
EN ISO 374-1:2016 /Type A	Chemicals	EN 16523:2015 permeation level			
	40% Sodium Hydroxide ( <b>K</b> )	6			

EN ISO 374-4:2019					
CAS number (K) 1310-73-2	<b>Class</b> Inorganic base				
Chemical 40% Sodium Hydroxide (K)	Average decrease % -33.0%				

Resistance to bacteria & fungi and virus

Air leak test – Pass

EN ISO 374-5:2016					
EN ISO 374-2:2014	Resistance to bacteria & fungi	Virus resistance			
VIRUS	PASS	PASS			
EN ISO 374-2:2014					

Water leak test – Pass

EN ISO 374-1:2016+A1:2018 Permeation levels are based on the following lead times:

-						
Performance level	1	2	3	4	5	6
Minimum breakthrough times (in min.)	>10	>30	>60	>120	>240	>480

## STORAGE REQUIREMENTS

The gloves should be stored in a clean, cool and dry place and not kept compressed in the original packaging. Do not expose the gloves to direct sunlight. Make sure that the packaging and the gloves are not damaged when shipped.

## **TESTING INSTITUTE**

These gloves are certified by: SATRA Technology Europe Ltd (Notified Body no. 2777), Bracetown Business Park, Clonee, Dublin D15 YN2P, Ireland.

# **DECLARATION OF CONFORMITY**

For a copy of the declaration of conformity, please refer to the following web link: www.oxxa-safety.com/doc

# **RELATED ITEMS**



**LATEX-THIN 44-140**ART. NO. 1.44.140.00



LATEX-STRONG 44-215 ART. NO. 1.44.215.00

## **YOUR SUPPLIER:**

(			,
Į.			